

The Silvershine™ CDM cutlery dryer performs several functions under its 304 stainless steel skin. Primarily to be used to eliminate the labor intensive task of drying flatware (stainless, silver plate, sterling) the Silvershine™ will retain cutlery's original shine, or over extended use can restore a shine to older cutlery. Using a UV-C germicidal lamp combined with heat the Silvershine™ also ensures a more complete removal of bacteria which might otherwise survive the dishwashing process.

The Silvershine™ is compact and mobile enabling it to move about any facility to where it is either needed most, or where it seamlessly blends into the kitchen procedure. With simple "plug and play" ability the machine is ready to begin work right away.

## CONSTRUCTION FEATURES

- \* 304 Stainless steel construction throughout
- \* Heavy duty 304 Stainless Steel exterior with polished finish to withstand tough kitchen environments
- \* Patented wide-mouth intake hopper for easy loading (CDM-6K and CDM-12K models only)
- \* Solid steel frame on constructed sub frame for years of use
- \* Patented INOX stainless steel NAUTILUS tub to withstand heat
- \* Powder-coated steel vibration grid
- \* Powerful ½ HP electric motor with efficient low amp. draw
- \* Protected UVC Germicidal lamp with automatic cut-off
- \* Tough ¼ inch thick plastic discharge chute
- \* Moisture resistant heavy duty steel springs (4) to transfer energy to frame
- \* Standard four (4) heavy duty castors, two (2) locking for maximum mobility

## PERFORMANCE FEATURES

- \* Long life calrod resistance point for higher operating temperatures
- \* Resistance point temperatures as high as 338°F for maximum sanitizing effect
- \* Germicidal lamp operating output of 253.7nm to eradicate bacteria
- \* Constant average operating temperature in NAUTILUS tub of 150°F -170°F for continuous sanitizing effect
- \* Simple four button control pad
- \* Easy to open service/fuse panel
- \* Pre-operation self diagnostic
- \* Internal clock system reminds when granulate replacement is necessary
- \* Granulate good for up to 400 hours of operation
- \* One button operation with safety shut-off
- \* Quiet, vibration free



304 STAINLESS CONSTRUCTION



"WIDE-MOUTH" HOPPER  
(Models CDM6K and CDM12K only)



POWDER-COATED VIBRATION GRID

## INCLUDED ACCESSORIES

- \* Custom bus bin with perforated insert
- \* Initial batch of vacuum sealed, dust-free vegetable granulate (20lb tub)
- \* Operations/maintenance manual


## AVAILABLE OPTIONS





- \* N/A (All features are standard)

## REPLACEMENT ITEMS

- \* Vacuum-sealed, dust-free vegetable granulate 20lb tubs (require replacing approx. 3X/year)
- \* Additional UV-C Lamps
- \* Additional custom bus bins with perforated inserts

UV-C LAMP SANITIZES CUTLERY





CAMPUS PRODUCTS INC. [www.cpushine.com](http://www.cpushine.com) (866) 912-3469

**SPECIFICATIONS**

Amps	4.6
Watts	1200
Dimensions (WxDxH)	18x22x20"
Volts	120
Shipping Weight	97 lbs.

*Silver*  
**shine**<sup>TM</sup>  
 Silvershine<sup>TM</sup> Model CDM-2K